



LubeRite™

Lubrication System

Fits many applications:
3 container sizes, 4 dispensing options to meet your specific need. Accessory pump, hoses and premium pouches are also available.

Three lids offer a choice of nozzle sizes; 1/4" (6mm), 1/2" (12mm) and 1" (25mm). Twist turn spout can be adjusted for the viscosity of your fluid to achieve the desired flow, from a high flow to a controlled pour.



Spout acts as a built in valve; it opens and closes to control flow, prevent spills and fully seals the system when closed. Spout directs liquids into tight places or a flexible extension hose can be added to reach awkward places.

Accessory Port is ideal for installing quick disconnect couplings and also great for obtaining samples for oil analysis without having to remove the entire lid, thereby reducing fluid contamination and moisture.

Port has 1/2" NPT female thread; Pump lid has two ports: 1/2" and 3/8" female thread.

Beefy, rustproof polyethylene lid is non-reactive and offers a fully sealed, leakproof system to prevent fluid contamination and eliminate spills. Strategically located Nitrile (Buna-N) o-rings inside lid, nozzle, accessory and quick fill ports ensure dirt and dust stay out for maximum cleanliness.



Anti-Fatigue On/Off Switch for breather vent provides smooth-flow pouring while allowing users a full five-finger grip while topping-off.

Quick Fill Port eliminates the need to open the entire lid and expose fluid to contaminants or risk spilling while refilling.

Cap on 15/16" ID port is attached with lanyard to prevent loss.

Large comfortable rounded handle accommodates a gloved hand for safe and easy transporting, and accurate pouring.

Square, stable shape makes the most of available storage space while flat drum surface allows more room for identification. Translucent color and graduated markings in English and metric make it easy to see liquid level.



Industrial strength (HDPE) drums with anti-static and UV inhibitor additives are ideal for lubricants that are engineered to withstand extreme temperatures.

"No Mistake" Color I.D. System

Identify fluids and reduce cross contamination with the simplest system ever.

Marked contents are clearly matched and visible in any of three ways:

- 1) color band on lid (8 color choices)
- 2) product label with blank box to write contents
- 3) matching color card in outside standard data pouch (4 two-sided cards for 8 matching color choices)

