





## EVO Condensate Neutralizer Technical Information




Sufficient volume of neutralizing agent is contained in the neutralizer to provide for 2000 hours of proper operation of a fully condensing appliance. PH should be checked annually and neutralizing agent replaced when the PH does not reach 6.5 or higher. Neutralizing agent used is 1/2" - 3/4" common limestone aggregate, p/n HWT 00101. PH Testing kit available, P/N MSC 33811.



Top View



Front View




Side View

### Companion Condensate Neutralizer

Bill of Material		Ratings & Dimensions							
Item	Description	Model	MBH	GPH	Lbs Media	A	B	C	D
1	1.5" PVC DWV Pipe	CNK 90001 V	200	2.2	3.5	8"	3.5"	20"	6"
2	1.5" x3" x 6" PVC Drum Trap w/Neutralizer Media	CNK 90001 VD	630	6.9	8	8"	3.5"	20"	12"
3	1.5" 90° PVC Elbow								


Note: These condensate assemblies can be used for Companion units HW79-HW599




Top View



Mounting base is not included. Neutralizer is intended to be mounted on EVO rack system.



Front View



Side View


### EVO 79-199 Condensate Neutralizer

Bill of Material		Ratings & Dimensions								
Item	Description	Model	Tees/Caps	MBH	GPH	Lbs Media	A	B	C	D
1	3" PVC DWV Pipe w/ Neutralizer Media	CNK 90001 M	1	200	2.2	7.0	30"	4"	2"	6"
2	3" PVC Sanitary Tee	CNK 90002 M	1	400	4.4	14.0	52"	4"	2"	6"
3	3" Galvanized Pipe Clamp	CNK 90003 M	2	600	6.6	21.0	75"	4"	2"	6"
4	1.5" 45° PVC Elbow and 3" x 1.5" PVC Coupler	CNK 90004 M	2	800	8.8	28.0	100"	4"	2"	6"
5	3" PVC Drain cap w/ predrilled holes for condensate lines	CNK 90005 M	3	1000	11	35.0	126"	4"	2"	6"
6	3" PVC Cap	CNK 90006 M	3	1200	13.2	42.0	144"	4"	2"	6"

Note: These condensate assemblies can be used for EVO Micro units HW79-HW199  
 The number of sanitary tees and caps increase with the size of the Neutralizer.

The EVO products these are applied to carry two or more of the following listings/certifications.





**EVO 299-599 Condensate Neutralizer**

Bill of Material		Ratings & Dimensions								
Item	Description	Model	Tees/Caps	MBH	GPH	Lbs Media	A	B	C	D
1	3" PVC DWV Pipe w/ Neutralizer Media	CNK 90001 D	1	630	6.9	8.5	30"	4"	2"	6"
2	3" PVC Sanitary Tee	CNK 90002 D	1	1260	13.8	16	52"	4"	2"	6"
3	3" Galvanized Pipe Clamp	CNK 90003 D	2	1890	20.7	23.5	75"	4"	2"	6"
4	1.5" 45° PVC Elbow and 3" x 1.5" PVC Coupler	CNK 90004 D	2	2520	27.7	31.0	100"	4"	2"	6"
5	3" PVC Drain cap w/ predrilled holes for condensate lines	CNK 90005 D	3	3150	34.6	37.5	126"	4"	2"	6"
6	3" PVC Cap	CNK 90006 D	3	3780	41.5	45.0	144"	4"	2"	6"

Note: These condensate assemblies can be used for EVO Micro units HW79-HW199  
 The number of sanitary tees and caps increase with the size of the Neutralizer.



**EVO 1499-1999 Condensate Neutralizer**

Bill of Material		Ratings & Dimensions					
Item	Description	Model	MBH	GPH	Lbs Media	A	B
1	4" PVC DWV Pipe w/ Neutralizer Media	CNK 90001 T	2000	22	20	34"	5"
2	4" PVC Cap						
3	4" Threaded PVC Plug						
4	4" PVC Female Adaptor						
5	5/8" x 1/2" Paraflex male elbow						
6	4" Galvanized Pipe Clamp w/ 1 5/8" Unistrut						

Note: These condensate assemblies can be used for EVO Trio units HW1499-HW1999

The EVO products these are applied to carry two or more of the following listings/certifications.

