



Safety Containers

A better solution for the containment of flammable wastes and flammable corrosives.

Justrite's Liquid Disposal Cans are made of high density polyethylene for superior chemical resistance and leak protection. Large and strategically placed opening offers controlled filling and pouring during disposal. Fixed position on handle allows lid to stay open for easy pouring. When closed, the cap automatically vents between



3 and 5 psig (0.2 and 0.35 bar). A flame arrester guards against outside ignition. Plated steel hardware is an economical choice. Stainless steel hardware offers the most protection against corrosives.

Poly cans come in safety red or translucent white which allows quick visual inspection of liquid level. **Model 12772** offers dual convenience of collecting liquids and withdrawing liquids in one single container.

Model No. 14724 and 14756 have a built-in polyethylene drum fill gauge indicator that pops-up to warn you when the container is almost full.

Red Liquid Disposal Cans New Item

Description and Capacity	Dimensions Outer Dia. x H (mm)	Approv./Lstg.	
		Regulation*	Model No.
2 gal (8L) polyethylene can w/plated steel hardware	12" x 14 ³ / ₄ "(305 x 375)	FM	14722
2 gal (8L) polyethylene can w/plated steel hardware with 08530 fill gauge built-in	12" x 14 ³ / ₄ "(305 x 375)	-	14724
2 gal (8L) polyethylene can w/stainless steel hardware	12" x 14 ³ / ₄ "(305 x 375)	FM	14762
5 gal (19L) polyethylene can w/plated steel hardware	12" x 20"(305 x 508)	FM	14755
5 gal (19L) polyethylene can w/stainless steel hardware	12" x 20"(305 x 508)	FM	14765
5 gal (19L) polyethylene can w/plated steel hardware with 08530 fill gauge built-in	12" x 20"(305 x 508)	-	14756 New
Replacement flame arrester, plated steel construction	-	-	11405
Replacement flame arrester, stainless steel construction	-	-	11406

White Liquid Disposal Cans New Item

Description and Capacity	Dimensions Outer Dia. x H (mm)	Approv./Lstg.	
		Regulation*	Model No.
2 gal (8L) polyethylene can w/stainless steel hardware	12" x 14 ³ / ₄ "(305 x 375)	FM	12751
5 gal (19L) polyethylene can w/stainless steel hardware	12" x 20"(305 x 508)	FM	12754
5 gal (19L) polyethylene can with stainless steel faucet	12" x 20"(305 x 508)	FM	12772 New



Safe, temporary collection of biological waste.

Justrite's Biohazard Waste Containers meet OSHA 29 CFR 1910.1030 for the segregation of infectious waste. They may be used to store contaminated laundry as well as other regulated waste (not to be used for sharps).

Sturdy steel cans feature leakproof construction with foot-operated, self-closing lid. Simple, foot pedal operation opens the container cover automatically to safely dispose of biohazard waste. Upon release of pedal, the can cover closes quickly to reduce the risk of contamination. A biohazard bag is held securely around the circumference of the can top. Optional label kit, #25880, offers compliance to California Health and Safety Code 118280 which requires the warning label to be visible from all sides of the container. Kit includes three labels and instructions.



Biohazard Waste Cans New Items

Description and Capacity	Dimensions Outer Dia. x H (mm)	Approv./Lstg. Regulation*	White Model No.	SoundGard™	SoundGard™
				White Model No.	Silver Model No.
6 gal (23L) biohazard can	11 ⁷ / ₈ " x 15 ⁷ / ₈ "(302 x 403)	FM	05910	05915	05914 New
10 gal (38L) biohazard can	13 ¹⁵ / ₁₆ " x 18 ¹ / ₄ "(354 x 464)	FM	05930	05935	05934 New
100 red liner bags, 11 microns thick	33" x 24"(838 x 610)	-	05901		
Code Compliant Label Kit for California (three labels and instructions)			25880 New		

05915
New SoundGard™ lid option offers a quiet close for those environments where it is desirable to lessen disruptive noise.

*See page 8 for Regulation Key.