PILOTS

"P" & "P5" Pilot

Watson McDaniel reserves the right to change the designs and/or materials of its products without notice. ©2006 Watson McDaniel Company

Pressure Pilot for HD & D Regulating Valves

Pressure

Pilot

- Outlet Pressure Range: 3-200 PSIG
- P-Pilot Standard for ± 1 PSIG accuracy
- P5-Pilot Special for \pm 0.5 PSIG accuracy



TYPICAL APPLICATIONS

The "P" or "P5" Pressure Pilots used with either the HD or D Regulator control steam pressure in steam mains or for process equipment. Pilot operated regulators will maintain constant downstream pressure even when the inlet pressure to the valve fluctuates or stream usage varies.

FEATURES

- The "P" Pilot can maintain downstream pressure to ±1 PSIG
- Optional "P5" Pilot can maintain downstream pressure to ±0.5 PSIG
- Choices of 3 overlapping pressure ranges
- In-line change of pressure control spring
- · Pilot installs using four bolts
- Full port strainer and blow-down valve on HD pilot adapter to eliminate failure caused by contaminated steam systems
- Can be used with temperature and solenoid control pilot
- Solid floating diaphragm
- Watson McDaniel's pilots can be used with other manufacturers regulators

OPTIONS

- Pressure pilot can be used with temperature pilot to eliminate the need for two separate regulators.
- Solenoid pilot can be added for remote on/off control of regulator
- \bullet P5 Options: Call factory for special "P5" Pilot which will maintain \pm 0.5 PSIG accuracy

RECOMMENDED PRESSURE

Differential Pressure: 10 PSIG minimum Minimum Inlet Pressure: 15 PSIG*

*Minimum Inlet Pressure for Temperature Regulator: 5 PSIG



MATERIALS	
Pilot Body & Cover	Ductile Iron
Gasket	Grafoil
Diaphragm	Phosphor Bronze
Head & Seat Assembly	Hardened SST (55Rc)

HOW TO ORDER

"P" or "P5" PRESSURE PILOT

Specify: • Reduced pressure range.

REGULATOR BODY

Specify:

- HD or D regulator body.
- · Regulator size or capacity.
- End connections

(threaded, 125/150/250/300# flanged).



