







# THE TECHNOLOGY:

The technology or structure behind each of the universal products helps determine the strength and absorbency of each sorbent. This information along with the product’s characteristics (grade, perforations, etc.) is what helps you decide which sorbent is best for your application.

All of these universal pads and rolls start with a highly absorbent meltblown polypropylene (MBPP) core - the difference is what happens from there...

|             |   |   |
|-------------|---|---|
| <b>MRO:</b> | MBPP coverstock is added to both sides of the core for additional durability and absorption capacity. Also, the coverstock generates less lint.   |   |
| <b>GP:</b>  | Pure and simple – Now MAXX enhanced, it’s a single ply, economy product.  |  |
| <b>UXT:</b> | Spunbond coverstock is added – making it virtually lint free, exceptionally strong, wringable and re-usable.  |  |
| <b>HT:</b>  | This hybrid features heavy-duty spunbond coverstock on top and a MBPP coverstock on the bottom – increasing durability and absorption while creating a tough work surface ideal for high traffic areas. |  |

| Feature:      | MRO  | GP  | UXT  | HT   |
|---------------|------|-----|------|------|
| Durability    | ✓✓✓  | ✓✓  | ✓✓✓✓ | ✓✓✓✓ |
| Low Linting   | ✓✓✓  | ✓✓  | ✓✓✓✓ | ✓✓✓✓ |
| Absorption    | ✓✓✓✓ | ✓✓✓ | ✓✓✓  | ✓✓✓✓ |
| Relative Cost | \$\$ | \$  | \$\$ | \$\$ |

+

## May We Also Suggest...

Don't forget this modular and mobile storage unit for storing your universal SPC sorbents. Strategically place them throughout your facility or take your spill control efforts on the go. Either way, you'll be better prepared for the leaks, drips and spills you deal with everyday. The Sorbent Center can be found on pages 36 and 37.

