

JRHF Series

Pressure Regulating Valves




The JRHF Series is a diaphragm operated, balanced trim pressure regulator. The choice between 1.5 and 1.9 Cv offers increased flows across the JRHF's 230 psi inlet range, while the PTFE soft seat provides ANSI Class VI shutoff. Four set spring ranges and three soft seal options offer the customer flexibility in a number of applications and environments. These valves are designed to regulate a variety of gases and liquids in applications where high flows and low control pressures are required.

Features:

- Top entry design facilitates in-line cleaning and maintenance
- Barstock construction guarantees material integrity and surface finish
- · Balanced trim offers high flows with minimal lockup
- Optimized internal volume
- Proprietary Jorlon diaphragm provides exceptionally long life
- PTFE or PEEK soft seat for ANSI Class VI shutoff



JRHF SERIES FLOW CONFIGURATIONS



\$10WFLOW

A Division of Jordan Valve 3170 Wasson Road Cincinnati, OH 45209

toll free. 800.543.7311 local. 513.533.5600 fax. 513.871.0105

www.lowflowvalve.com

Top View

SPECIFICATIONS



JRHF SERIES SPECIFICATIONS

Line Size: ½", 3/4", 1" (DN15, DN20, DN25)

End Connections

- Threaded
- Socket Weld
- Flanged

Materials

- PTFE soft seat to +150°F (+66°C)
- PEEK soft seat to +250°F (+177°C)
- 316L SST- Standard
- Contact factory for other body/trim/seat materials

Diaphragm Material: Jorlon

Maximum Inlet Pressure: 230 psig (16 bar)

Pressure at Maximum Temperature: 150 psi @ 275°F

Spring Ranges

- 0-20 psi (0 1,4 bar)
- 0-50 psi (0 3,4 bar)
- 0-100 psi (0 6,9 bar)
- 0-150 psi (0 10,3 bar)

Flow Characteristics

Cv 1.5 for 1/2", Cv 1.9 for 3/4" and 1"

Options

- Panel Mounting
- Captured Vent
- Locking Wire
- Tamper Proof
- Lockout Device

OPTIONS & DEFINITIONS

Panel Mount The panel mount feature utilizes a threaded spring housing and a panel mount ring to secure the regulator to an instrument panel. This option requires a 1-1/2" panel cut out.

Captured Vent The captured vent design provides maximum safety for the user when handling toxic or hazardous media. It features a 1/8" FNPT port located on the spring housing. The user can easily tube this vent to a safe location. This option can be incorporated into a self-relieving regulator that provides an additional port to permit the safe expulsion of hazardous media.

Locking Wire The locking wire option utilizes a lead sealed metal wire to physically hold the adjusting screw in place to prevent any unwanted set point changes.

Tamper Proof The tamper proof option replaces the standard adjusting knob with a stainless steel acorn nut.

Lockout Device The lockout device is a 2 piece polypropylene enclosure which encapsulates the adjustment knob and prevents unwanted set point changes. The part number required for this valve is 26971. (Lock not included)

JRHF SIZING

- Use the "LVCV Sizing Software" link found on the www.lowflowvalve.com home page and navigate to LowFlow valve sizing.
- 2. Use the software to size for flow using the listed CV of the valve and the customer's application conditions.
- 3. The JRHF is rated to 60% of the flow value found using LVCV. There is no low-end cutoff limit.


Example:

Air, ambient temperature, P1 = 200 psi, P2 = 80 psi, 1" schedule 40 pipe, flow rate 7,800 SCFH


Using LVCV to size for flow we find that these conditions and a 1.9 CV will result in a maximum flow of 13,212 scfh. Multiply this value by 0.60 to find the maximum rated flow for the JRHF-100-6L. Your result will be 7,927 scfh (13,212 x 0.6 = 7,927). Any flow below this result is acceptable for the valve.



JRHF SERIES FEATURES AND BENEFITS



JRHF DIMENSIONS



VALVE SIZE	DI	MENSION	IS, INCH	S	WEIGHT,
VALVE SIZE	A	В	C	D	LBS
1/2" 3/4" 1"	6.29	1.02	3.50	3.85	9

VALVE SIZE		DIMENSI	ONS, MM		WEIGHT,
VALVE SIZE	A	В	C	D	KGS
DN15, DN20, DN25	160	26	89	98	4,1



ORDERING SCHEMATIC

JRHF SERIES ORDERING SCHEMATIC

1	Model		Size		Material		1 & 2	3 & 4	5 & 6	7 & 8	9 & 10	11 & 12	13 & 14	15	16	17
		-		-		/										

JRHF	Pressure Reducing Valve	
	Size	
050	1/2"	
075	3/4"	

100

Model

	Material	
6L	Stainless Steel 316L	

1 & 2		Body Fea	ature
End	Connection	Por	t Configuration
С	FNPT	A	Port "A"
		В	Port "B"
		C	Port "C"
		D	Port "D"
		E	Port "E"
ZZ	Non-Standar	d	

3 & 4	Trim	
1E	EPDM & 6L	
1V	VIT & 6L	
1K	Buna-N & 6L	
ZZ	Non-Standard	

5 & 6	Seat Material	
TF	PTFE (1/2" 1.5 Cv) 1.9 Cv	
PK	PEEK (1/2" 1.5 Cv) 1.9 Cv	
ZZ	Non-Standard	

7 & 8	Range Spring/Outlet Pressure
02	0-20 PSI
05	0-50 PSI
10	0-100 PSI
15	0-150 PSI
ZZ	Non-Standard

9 & 10	Diaphragm Material	
JL	Jorlon	
ZZ	Non-Standard	

11 & 12	Actuator	
SK	Standard	
PM	Panel Mount	
ZZ	Non-Standard	

13 & 14	Inlet Gauge
AA	0-30 PSIG/BAR (Dual)
BB	0-60 PSIG/BAR (Dual)
CC	0-100 PSIG/BAR (Dual)
DD	0-160 PSIG/BAR (Dual)
EE	0-200 PSIG/BAR (Dual)
FF	0-300 PSIG/BAR (Dual)
ON	None
ZZ	Non-Standard

15	Outlet Gauge
0A	0-30 PSIG/BAR (Dual)
0B	0-60 PSIG/BAR (Dual)
OC	0-100 PSIG/BAR (Dual)
0D	0-160 PSIG/BAR (Dual)
0E	0-200 PSIG/BAR (Dual)
ON	None
Z	Non-Standard

16	SEP Compliance
G	SEP Compliant
Z	Non-Standard

17	Accessories
S	Clean for Oil Free*
X	Clean for Oxygen*
Z	Non-Standard

^{*}Consult factory for compatible gauge options

LowFlow Valve reserves the right to make revisions to its product, specifications, literature and related information without notice. Please visit our website at www.lowflowvalve.com for the latest information on our products.

